

Olympic Wire and Cable

7 Madison Road Fairfield, NJ 07004

973.227.7996 800.526.2269 Fax: 973.227.1606

email: sales@olympicwire.com

Olympic P/N 6318E, TPE Jacket Coiled Cords, SVEO, SJEOW, SEOW



TPE Jacket Coiled Cords, SVEO, SJEOW, SEOW

Retracted Lengths 1, 2 & 4 Feet - Extended Lengths 5, 10 & 20 Feet

Long-lasting service is assured with this quality multiconductor power cord. Each conductor is stranded copper, with TPE insulation, and a rugged weather and oil resistant TPE jacket overall.

Application:

Used on electric tools, portable drills, soldering irons, electrical appliances, household appliances, etc., to eliminate loose hanging wires and to prevent wires from tangling and twisting.

SPECIFICATIONS

Conductor Size	18 AWG
Stranding	41/34, Bare Copper
No. of Conductors	3
Insulation	TPE
Jacket	TPE, Black
Cable O.D.	1 3/8 in
Coil O.D.	0.308 in
UL Style	SJEOW
CSA Type	SJTOW
Color Code	Black, White, Green
Voltage	300 V
Operating Temperature	-20 to +90 °C
Cord Length	4 ft
AMP Rating	7
Tangent Leads ¹	6 in

RoHS Compliant



RoHS Compliant

1 12 inch retracted lengths have 12 inch tangent leads. 24 inch, 36 inch, and 48 inch retracted lengths have 6 inch tangent leads.