

## Olympic Wire and Cable

7 Madison Road Fairfield, NJ 07004

973.227.7996 800.526.2269 Fax: 973.227.1606

email: sales@olympicwire.com

### Olympic P/N 6355E, TPE Jacket Coiled Cords, SVEO, SJEOW, SEOW

#### TPE Jacket Coiled Cords, SVEO, SJEOW, SEOW

**Retracted Lengths 1, 2 & 4 Feet - Extended Lengths 5, 10 & 20 Feet**

Long-lasting service is assured with this quality multiconductor power cord. Each conductor is stranded copper, with TPE insulation, and a rugged weather and oil resistant TPE jacket overall.

**Application:**

Used on electric tools, portable drills, soldering irons, electrical appliances, household appliances, etc., to eliminate loose hanging wires and to prevent wires from tangling and twisting.



### SPECIFICATIONS

Conductor Size	16 AWG
Stranding	65/34, Bare Copper
No. of Conductors	4
Insulation	TPE
Jacket	TPE, Black
Cable O.D.	1 3/8 in
Coil O.D.	0.365 in
UL Style	SJEOW
CSA Type	SJTOW
Color Code	Black, White, Green, Red
Voltage	300 V
Operating Temperature	-20 to +90 °C
Cord Length	4 ft
AMP Rating	8
Tangent Leads <sup>1</sup>	6 in

RoHS Compliant



RoHS Compliant

1 12 inch retracted lengths have 12 inch tangent leads. 24 inch, 36 inch, and 48 inch retracted lengths have 6 inch tangent leads.