

**Olympic Wire and Cable**

7 Madison Road • Fairfield, NJ 07004

973.227.7996 800.526.2269 • Fax: 973.227.1606

email: sales@olympicwire.com

---

**Olympic P/N 6379P, PVC Jacketed Communications and Electronic Coil Cord**

---

**PVC Jacketed Communications and Electronic Coil Cord**


**Retracted Lengths 1, 2, 3 & 4 Feet - Extended Lengths 5, 10, 15 & 20 Feet**  
Stranded tinned copper, Polypropylene insulated, PVC Jacketed.



---

**SPECIFICATIONS**

Available Length (Retracted)	12 in 24 in 36 in 48 in
No. of Conductors	15
Conductor Size	23 AWG
Voltage	300 V
Nom. Area	0.259 mm <sup>2</sup>
Stranding	21/36 Tinned Copper
Insulation	Polypropylene
Jacket	PVC, Black
AMP Rating	1
Cable O.D.	0.310 in
Coil O.D.	1 1/16 in
UL Style	2464

Color Code	Black Blue Brown Gray Green Green/Black Orange Pink Purple Red Red/Black Tan White White/Black Yellow
CSA Type	AWM
Operating Temperature	-20 to +80 °C
Tangent Leads <sup>1</sup>	6 in 12 in
RoHS Compliant	 RoHS Compliant

<sup>1</sup> 12 inch retracted lengths have 12 inch tangent leads. 24 inch, 36 inch, and 48 inch retracted lengths have 6 inch tangent leads.