

Universal Tongue-Operated Safety Interlock Switch

- Strong and versatile—the compact size of the strong, glass-filled polyester housing and metal reinforced cam allows this popular switch to be used in most applications
- NEMA 6 enclosure enables these switches to withstand water washdown cleaning
- Rotatable head gives four possible actuator entry points for versatile installation. A blanking plug is supplied for the unused entry
- Small swing radius allows use on doors with a swing radius as small as 2.5 in. when using the optional flexible actuators
- Hi-Hold models reduce nuisance rips and allow the switch to also serve as the gate catch without the need to mount any additional hardware
- 4 contact poles provide 2 poles for dual channel safety monitoring and 2 additional poles for status monitoring



Conforms to EN1088, EN292, EN60947-5-1, EN60204-1
UL and C-UL listed

- Optional connector makes installation easy
- Optional stainless steel head is available

Rapid Delivery Ordering Information

Model	Part Number	Description
T5009-021F1M	44501-0120	T5009 BASE MODEL, FLX1 2N/C+1NO BBM, 3 X M20/NPT
T5009-021SM	44501-0110	T5009 BASE MODEL, 2NC+1NO BBM, STD ACTUATOR, 3 X M20/NPT
T5009-6040N	44501-1045	T5009-6 BASE MODEL, 4NC BBM, 3 X 1/2 NPT
SM01-MCK40	44501-0740	T5009 CATCH KIT
SA01-S	44501-0750	T5009 REPLACEMENT STANDARD ACTUATOR
SA01-STD	44501-0755	T5009 STANDARD SPARE ACTUATOR, PLASTIC HEADED SWITCHES
SA01-FLX1	44501-0760	T5009 FLEX 1 SPARE ACTUATOR, PLASTIC OR STAINLESS STEEL HEADED SWITCHES
SA01-FLX2	44501-0765	T5009 FLEX 2 SPARE ACTUATOR, PLASTIC OR STAINLESS STEEL HEADED SWITCHES
SA01-F2	44501-0780	T5009, T5007 REPLACEMENT FLEXIBLE 2 ACTUATOR WITH GUIDE
SA19-F1	44519-0710	T5009, TL8012, TL5012, T5007, T4011 REPLACEMENT FLEXIBLE ACTUATOR WITH GUIDE
SLD26-01	44526-0801	T5009, T4011, T5007, TL8012-S SWITCH LOCKING DEVICE