

[All Categories](#) > [Sensing](#) > [Proximity Sensors](#) > [Compact - Cylindrical](#) > [E2B DC 3-Wire Long Barrel](#) > Item # E2B-S08LS01-WP-B2 5M

Item # E2B-S08LS01-WP-B2 5M, E2B Series 1 mm Sensing Distance Proximity Sensor with 5 m Polyvinyl Chloride (PVC) Cable

Request Information

[Printable Page](#) [Download PDF](#) [Email This Page](#)



Single M8 Long Polyvinyl Chloride (PVC) Cable 5M Positive-Negative-Positive (PNP) Normally Closed (NC)

DOWNLOADS

- [Flyer: Factory Molded Connector Program for Omron Sensors, 2013](#)
- [E2B Cylindrical Proximity Sensor Datasheet](#)
- [E2B Cylindrical Proximity Sensor Brochure](#)

Specifications

Type	Proximity Sensor
Output Type	3-Wire Direct Current (DC), Positive-Negative-Positive (PNP)
Sensor Type	Inductive
DC Voltage	12 to 24 V
Size	M8
Shield Type	Shielded
Polyvinyl Chloride (PVC) Cable Length	5 m
Contact Configuration	Normally Closed (NC)
Case Material	Stainless Steel
Threaded Length	49 mm
Overall Length	64 mm
Electrical Connection	5 m Polyvinyl Chloride (PVC) Cable
Sensing Distance	1 mm

News

Product News
Corporate News

Company Info

About Omron
Omron Principles

Careers

Awards
Giving Back

Contact

Omron in United States
Contact Us

Follow us

Facebook

[Omron on Social Media](#)

[Company Profile](#)

[Summer Internships](#)

[Global presence](#)

 [Twitter](#)

[eNews](#)

[Business Fields](#)

[Events](#)

 [LinkedIn](#)

[Giving Back](#)

 [Youtube](#)

[Environmental](#)

[Omron Americas](#) [Omron Corporation](#) [Legal Notices](#) [Privacy Policy](#) [Sitemap](#)

Copyright © Omron Corporation 2017. All rights reserved.