

[All Categories](#) > [Accessories](#) > [Connector Cordsets](#) > [Standard Cordset](#) > [XS2WM](#) > Item # XS2W-M12PVC4SA5M

Item # XS2W-M12PVC4SA5M, 5 m Length Standard Cable with M12 Connector

Request Information

[Printable Page](#) [Download PDF](#) [Email This Page](#)



Sensor I/O Extension Cordset, Socket and Plug , PUR or PVC Cable

Specifications

Type	Standard Cable with M12 Connector
Connection Type	M12
Wire Size	22 AWG
Length	5 m
Number of Wires	4
Connector Shape	Straight, Angled
Socket or Plug	Plug-Socket
Cable Material	Polyvinyl Chloride (PVC)
DC Voltage	125 V
AC Voltage	250 V
Cable Diameter	6 mm
Crimping or Solder	Crimp

DOWNLOADS

- [XS2F-M12 Single Ended Cables with M12 Connectors](#)
- [Data Sheet: XS2_M12 Connector Cables](#)
- [XS2 M12 Molded Sensor I/O Connectors Data Sheet](#)
- [XS2 Round Water-resistant Connectors \(M12\) Data Sheet](#)
- [XS2_M12 Round Water Resistant Connectors Data Sheet, XS2W, XS2F, XS2H, XS2G, XS2C, XS2P, XS2R, XS2M](#)
- [M8/M12 Sensor Connector Selection Guide: XS2, XS3, XS5](#)
- [XS5, XS2 Assembly Tooling and Accessories Data Sheet](#)
- [Y96E Connector Cables Data Sheet](#)

News

- [Product News](#)
- [Corporate News](#)
- [Omron on Social Media](#)
- [eNews](#)

Company Info

- [About Omron](#)
- [Omron Principles](#)
- [Company Profile](#)
- [Business Fields](#)

Careers

- [Awards](#)
- [Giving Back](#)
- [Summer Internships](#)

Contact

- [Omron in United States](#)
- [Contact Us](#)
- [Global presence](#)

Follow us

- [Facebook](#)
- [Twitter](#)

Events

Giving Back

Environmental

 LinkedIn

 Youtube

[Omron Americas](#) [Omron Corporation](#) [Legal Notices](#) [Privacy Policy](#) [Sitemap](#)

Copyright © Omron Corporation 2017. All rights reserved.
