
EASY Hybrid Remote | User interfaces for light management systems



Areas of application

- Shop lighting
- Restaurants

Product features

- Convenient radio and infrared remote control for EASY control units
- Hybrid technology for digital infrared and 868.3 MHz radio remote control
- Operation of up to 8 lighting scenes, 8 lighting groups and 4 sequences
- LCD with user-definable backlighting

Product datasheet

Technical data

Dimensions & weight



Length	187.0 mm
Width	57.0 mm
Height	23.0 mm
Product weight	240.00 g

Colors & materials

Product color	Black
----------------------	-------

Temperatures

Ambient temperature range	0...+40 °C
----------------------------------	------------

Capabilities

Dimming interface	EASY
Transmitter range	30 / 15 m ¹⁾

¹⁾ Radio / Infrared

Certificates & standards

Type of protection	IP20
---------------------------	------






Equipment / Accessories

- Docking station for wall mounting included

Download Data

File

Product datasheet

	Declarations of conformity Declaration of conformity EASY Color Drive EASY Hybrid Remote EASY RC radi
	Installation/Operation notice EASY Hybrid Remote Technical instructions
	Installation/Operation notice EASY Hybrid Remote Technical instructions
	Installation guide EASY Hybrid Remote
	Product movie EASY HYBRID REMOTE TUTORIAL (G)

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321421739		Shipping carton box 5	265 mm x 215 mm x 220 mm	12.53 dm ³	2401.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.