

# 1900

## MityLite™ 1900 Flashlight



### Overview

Unlike conventional flashlights that have a yellowish beam, the MityLite 1900 flashlight uses a hi-intensity Xenon lamp that produces a powerful, bright beam. Use this compact flashlight to cut through thick smoke, fog, and dust. It is submersible and comes with a twist-on shroud. The 1900 is ideal for any situation. Powered by 2 AAA alkaline cells.

- Built Pelican tough
- Unconditional Lifetime Guarantee of Excellence
- **Submersible**
- **Super bright Xenon beam**

**Body:** Xenoy Polymer Resin

**Lens:** Polycarbonate Resin

**Shroud:** Xenoy Polymer Resin  
**Switch Type:** Twist On/Off Lens Shroud  
**Modes:** On/Off  
**Contact, Spring & Retainer:** Phosphore/Bronze  
**O-Ring:** Ethylene Propylene

Minimum Pack 12 ea.  
 Packaged Weight: 2.4 oz.

## COLORS




## CONFIGURATIONS

**1900** MityLite™ 1900 Flashlight (Carded)  
 MityLite™ 1900 Flashlight (Clear Gift Tube)  
 Individually packed in tubes (no display).  
**1900T** Includes 2 AAA-cell Energizer???? alkaline batteries.  
 Minimum Pack 12 ea.

NSN #6230-01-518-2061 - 1900TNVG Black  
 NSN #6230-01-365-7647 - 1900T Orange  
 NSN #6230-01-324-2950 - 1900T Orange  
 NSN #6230-01-463-8505 - 1900C  
 NSN #6230-01-281-3774 - 1900LM  
 NSN #6230-01-345-6314 - 1900T Black  
 NSN #6230-01-522-3357 - 1900C Yellow

## Specs

### APPROVALS

 Class I, Div. 2; Gp ABCD, T3C; Class II; Div. 2; Gp G.



us Class I, Div. 1, GP C,D, T3C CONFORMS TO STD UL 783

**IECEx** Ex ib e IIC T4 IP67 IEC Ex TSA 06.0021X

IPX4 = Water Resistant

IPX7 = Water Proof (submerged to 1 meter for 30 min.)

IPX8 = Submersible (submerged to 100 meters for 4 hours)

### ACCESSORIES



**1904 MityLite™ 1900 Lamp Module**  
 Lamp module packaged on a color hang card.  
 Minimum Pack 6 ea. WT.: 4.6 OZ.

Accessories shown are for reference only, and are subject to change at manufacturers discretion.

## SIMILAR PRODUCTS



**MityLite™ 1900NVG Flashlight**



**MityLite™ 1960 LED Flashlight**



**Nemo™ 1960 LED Flashlight**

800.473.5422

---

All trademarks are registered and/or unregistered trademarks of Pelican Products, Inc., its subsidiaries and/or affiliates.  
© 2015 Pelican Products, Inc.