

## Zack marker strip - ZB 3,5,LGS:FORTL.ZAHLEN 81-90 - 0801404:0081


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Zack marker strip, 10-section, horizontally labeled with the consecutive numbers: 81 ... 90, white, width: 3.5 mm



The figure shows the ZB 3,5:UNBEDRUCKT, - LGS:FORTL.ZAHLEN, - QR:FORTL.ZAHLEN, and CUS versions

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 046356 665391
GTIN	4046356665391
Weight per Piece (excluding packing)	1.000 g
Custom tariff number	49119900
Country of origin	Germany

### Technical data

Color	white
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

### Ambient conditions

Temperature range	-40 °C ... 100 °C
-------------------	-------------------

### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V2

## Zack marker strip - ZB 3,5,LGS:FORTL.ZAHLEN 81-90 - 0801404:0081

### Classifications

#### eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141100
eCl@ss 6.0	27141100
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137
eCl@ss 9.0	27141137

#### ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761
ETIM 6.0	EC000761
ETIM 7.0	EC000761

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131505