

Magazine - BLUEMARK MAG WM-M (D30) - 0802747

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Magazine, width: 76 mm, color: white



Your advantages

In conjunction with the BLUEMARK CLED printer, the magazine for accommodating WMTB-AL... ensures printing with a high degree of positioning accuracy.

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 845854
GTIN	4046356845854
Weight per Piece (excluding packing)	50.000 g
Custom tariff number	90179000
Country of origin	Germany

Technical data

Dimensions

Length (b)	120 mm
Width (a)	76 mm

General

Color	white
Material	POM

Classifications

eCl@ss

eCl@ss 10.0.1	19149290
eCl@ss 4.0	24190200

Magazine - BLUEMARK MAG WM-M (D30) - 0802747

Classifications

eCl@ss

eCl@ss 4.1	24190200
eCl@ss 5.0	19029100
eCl@ss 5.1	19029100
eCl@ss 6.0	19140100
eCl@ss 7.0	19140190
eCl@ss 8.0	19149290
eCl@ss 9.0	19149290

ETIM

ETIM 3.0	EC001675
ETIM 4.0	EC001675
ETIM 5.0	EC001675
ETIM 6.0	EC001675
ETIM 7.0	EC001675

UNSPSC

UNSPSC 6.01	43172501
UNSPSC 7.0901	43212107
UNSPSC 11	43172501
UNSPSC 12.01	43212107
UNSPSC 13.2	43211612
UNSPSC 18.0	43211612
UNSPSC 19.0	43211612
UNSPSC 20.0	43211612
UNSPSC 21.0	43211612