

Marker carriers - UBE/D (60X10) - 0803719

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Terminal strip marker carrier for identifying terminal groups, for installation on the NS 32 or NS 35/7.5 terminal strips, marking field size: 60 x 10 mm

RoHS

Key Commercial Data

Packing unit	1 STK
Minimum order quantity	50 STK
GTIN	 4 055626 146263
GTIN	4055626146263
Weight per Piece (excluding packing)	8.000 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length (b)	48.5 mm
Width (a)	10 mm
Height	60 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

General

Color	gray
Base element material	PA
Components	free from silicone and halogen

Marker carriers - UBE/D (60X10) - 0803719

Technical data

General

Flammability rating according to UL 94	V0
RoHS compliant	Yes
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Marking mounting type	DIN rail mounting

Standards and Regulations

Flammability rating according to UL 94	V0
--	----