

Shrink sleeve - WMS 9,5 (30X16)RL - 0804267

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOMARK W, THERMOMARK ROLL, THERMOMARK X1.2, THERMOMARK ROLL X1, perforated, Mounting type: slide on, Lettering field: 30 x 16 mm



The illustration shows WMS 6,4 (30X10)R



Key Commercial Data

Packing unit	1 STK
Weight per Piece (excluding packing)	450.000 g
Custom tariff number	39173200
Country of origin	China

Technical data

Dimensions

Length (b)	30 mm
Width (a)	16 mm
Cable diameter	9.5 mm

General

Color	white
Base element material	polyolefine
Components	Halogen-free
Material	Polyolefine
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	2000
Marking mounting type	slide on

Standards and Regulations

Shrink sleeve - WMS 9,5 (30X16)RL - 0804267

Technical data

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Approvals


Approvals


Approvals

CSA / UL Recognized

Ex Approvals

Approval details

CSA		http://www.csagroup.org/services/testing-and-certification/certified-product-listing/	252259
-----	-------------------------------------------------------------------------------------	-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	--------

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 310982
---------------	-------------------------------------------------------------------------------------	-------------------------------------------------------------------------------------------------------------------------------------------------------	---------------
