

## Marking foil for zack marker strip - TML (101X4,2)R TR - 0816621

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marking foil for zack marker strip, Roll, transparent, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, THERMOMARK ROLL X1, Mounting type: Adhesive, Lettering field: 101 mm x 4.2 mm

### Product Features

- The TML labeling range offers the option of subsequent labeling of zack marker strip and flat zack marker strip materials using a marking foil
- Labeling service: Phoenix Contact can custom-label all TML markers according to your requirements
- The markers that are supplied in roll format can be labeled quickly and cost-effectively using THERMOMARK printers

### Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	210.7 g
Custom tariff number	39199000
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	101 mm
Width (a)	4.2 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
---------------------------------	-------------------

#### General

Color	transparent
Components	Silicone-free
Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	2500
Number of individual labels per row	10
Marking mounting type	Adhesive

### Standards and Regulations

## Marking foil for zack marker strip - TML (101X4,2)R TR - 0816621

### Technical data

#### Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

### Classifications

#### eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27149129

#### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001288

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410