

## Conductor marker - UC-WMC 7,5 (23X8) BU - 0818946

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marker, Sheet, blue, unlabeled, can be labeled with: BLUEMARK CLED, BLUEMARK LED, Plotter, Mounting type: clip on, Cable diameter: 5-7.5 mm, Lettering field: 23 x 8 mm

### Product Features

- The UC-WMC ... UniCard labeling range includes markers for captive labeling of control lines to cable sheaths with large diameters
- Can be clipped on even after wiring has been completed
- One-handed assembly
- Two labeling areas that are clearly legible at all times
- The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- The markers support multi-line labeling
- The sheets provide space for including function texts
- The format automatically ensures printing with a high degree of positioning accuracy

### Key Commercial Data

|                                      |          |
|--------------------------------------|----------|
| Packing unit                         | 1 pc     |
| Minimum order quantity               | 5 pc     |
| Weight per Piece (excluding packing) | 16.0 g   |
| Custom tariff number                 | 39269097 |
| Country of origin                    | Poland   |

### Technical data

#### Dimensions

|                |                 |
|----------------|-----------------|
| Width (a)      | 23 mm           |
| Cable diameter | 5 mm ... 7.5 mm |

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
|---------------------------------|-------------------|

#### General

|       |      |
|-------|------|
| Color | blue |
|-------|------|

## Conductor marker - UC-WMC 7,5 (23X8) BU - 0818946

### Technical data

#### General

|  |                                |
|--|--------------------------------|
| Components                             | free from silicone and halogen |
| Flammability rating according to UL 94 | V2                             |
| Material                               | PA                             |
| Wipe resistance                        | DIN EN 61010-1 (VDE 0411-1)    |
| Number of individual labels            | 6                              |
| Number of individual labels per row    | 2                              |
| Marking mounting type                  | clip on                        |

#### Standards and Regulations

|  |                             |
|--|-----------------------------|
| Wipe resistance                        | DIN EN 61010-1 (VDE 0411-1) |
| Flammability rating according to UL 94 | V2                          |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27400401 |
| eCl@ss 6.0 | 27400401 |
| eCl@ss 7.0 | 27400401 |
| eCl@ss 8.0 | 27400401 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC001530 |
| ETIM 5.0 | EC001530 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39121410 |