

Conductor marker carrier - PATO 1/18 - 0823740

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Conductor marker carrier, transparent, unlabeled, mounting type: clip on, cable diameter range: 2 ... 3.5 mm, lettering field size: 4 x 18 mm

Your advantages

- Can be labeled using UC-WMT ... and US-WMT ... plastic labels or EMT insert strips
- These marking collars are used for subsequent labeling of systems that have already been wired

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	500 pc
GTIN	 4 046356 333658
GTIN	4046356333658
Weight per Piece (excluding packing)	0.540 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length (b)	18 mm
Width (a)	5.6 mm
Cable diameter	2 mm ... 3.5 mm

Ambient conditions

Ambient temperature (operation)	-50 °C ... 80 °C
---------------------------------	------------------

Conductor marker carrier - PATO 1/18 - 0823740

Technical data

General

Color	transparent
Type	Profile
Components	Silicone-free
Flammability rating according to UL 94	V0
Material	PVC
Marking mounting type	clip on

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Classifications

eCl@ss

eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27149100
eCl@ss 7.0	27149153
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC002248
ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504

Conductor marker carrier - PATO 1/18 - 0823740

Classifications

UNSPSC

UNSPSC 20.0	39131504
UNSPSC 21.0	39131504