

Conductor marking collar - SD-WMS 3 (NU) YE:6 - 0825544:6

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Conductor marking collar, Labeled with the number: 6, yellow, Width: 3.2 mm

The figure shows a version of the article

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	200 pc
Weight per Piece (excluding packing)	0.0050 g
Custom tariff number	39269097
Country of origin	Sweden

Technical data

Color	yellow
Flammability rating according to UL 94	V0
Components	Free from silicone and cadmium

Ambient conditions

Temperature range	-30 °C ... 60 °C
-------------------	------------------

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27400401

Conductor marking collar - SD-WMS 3 (NU) YE:6 - 0825544:6

Classifications

eCl@ss

eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27149129

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410