

Shock protection - EMPPR (27X15) - 0829535

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Shock protection, Sheet, transparent, unlabeled, Mounting type: snapped into marker carrier, Lettering field: 27 x 15 mm



Product Features

- ✓ High level of mechanical and chemical stability
- ✓ Suitable for permanent outdoor use
- ✓ Stuck or snapped onto labeled CARRIER ... to protect the labeling
- ✓ Extremely thick, yet flexible and transparent shock protection

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	50 pc
Weight per Piece (excluding packing)	0.02 g
Custom tariff number	39204910
Country of origin	Germany

Technical data

Dimensions

Length (b)	27 mm
Width (a)	15 mm

Ambient conditions

Ambient temperature (operation)	-30 °C ... 70 °C
Recommended storage conditions	10-30 °C / 40-70 % relative humidity. Storage in a cool and dry place is recommended.

General

Color	transparent
Components	Silicone-free
Flammability rating according to UL 94	V0
Material	PVC

Shock protection - EMPPR (27X15) - 0829535

Technical data

General

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
RoHS compliant	Yes
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	Following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Foil strength	300 µm
Marking mounting type	snapped into marker carrier

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 4.0	24190218
eCl@ss 4.1	24190218
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27149129

ETIM

ETIM 4.0	EC002848
ETIM 5.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
-------------	----------

Shock protection - EMPPR (27X15) - 0829535

Classifications

UNSPSC

UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410