

Cable marker carrier - KMK HP (29X8) - 0830721

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Cable marker carrier, transparent, unlabeled, mounting type: Assembly with cable binders, cable diameter: ≥ 6 mm, lettering field size: 29 x 8 mm



Your advantages

- Plastic cable markers for insert labels, for assembly with cable binders
- Plastic cable markers for marking and bundling conductors and cables indoors
- The markers have eyelets and are attached with cable binders
- The marked insert label is protected from dirt by the sealing cap

Key Commercial Data

Packing unit	1 pc
Minimum order quantity	100 pc
GTIN	 4 046356 725798
GTIN	4046356725798
Weight per Piece (excluding packing)	2.000 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length (b)	29 mm
Width (a)	8 mm
Height (c)	29 mm

Ambient conditions

Cable marker carrier - KMK HP (29X8) - 0830721

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
Ambient temperature (assembly)	-40 °C

General

Color	transparent
Type	Mounting set
Components	halogen-free
Flammability rating according to UL 94	V0
Material	PC (polycarbonate)
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Marking mounting type	Assembly with cable binders
Result	Test passed
Class I	3
Class F	1
R22	HL 3
R24	HL 3

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 10.0.1	27400401
eCl@ss 4.0	27061700
eCl@ss 4.1	27061700
eCl@ss 5.0	27400400
eCl@ss 5.1	27400400
eCl@ss 6.0	27149100
eCl@ss 7.0	27149153
eCl@ss 8.0	27400401
eCl@ss 9.0	27400401

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC002248

Cable marker carrier - KMK HP (29X8) - 0830721

Classifications

ETIM

ETIM 6.0	EC001530
ETIM 7.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504
UNSPSC 18.0	39131504
UNSPSC 19.0	39131504
UNSPSC 20.0	39131504
UNSPSC 21.0	39131504

Accessories

Accessories

Cable tie

Cable tie - WT-HP HF 3,6X140 - 0830982



Cable binders for quick and secure bundling, standard version

Cable tie - WT-HP HF 4,8X200 - 0830983



Cable binders for quick and secure bundling, standard version

Cable marker carrier - KMK HP (29X8) - 0830721

Accessories

Cable tie - WT-HP HF 4,5X290 - 0830984



Cable binders for quick and secure bundling, standard version

Conductor marking

Insert label - EMT (29X8)R - 0817277



Insert label, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK ROLL X1, THERMOMARK ROLL 2.0, THERMOMARK ROLL, mounting type: insert, cable diameter range: 10 ... 25 mm, lettering field size: 29 x 8 mm, Number of individual labels: 5400

Device marking

Snap-in markers - UCT-EMP (29X8) - 1014118



Snap-in markers, Sheet, white, unlabeled, can be labeled with: TOPMARK NEO, TOPMARK LASER, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 29 x 8 mm, Number of individual labels: 15

Snap-in markers - US-EMP (29X8) - 0829436



Snap-in markers, Card, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, mounting type: snapped into marker carrier, lettering field size: 29 x 8 mm, Number of individual labels: 48