

## Marker for terminal blocks - UM1-TM (8X10) - 0830906

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Markers for marking terminal blocks from Weidmüller, Conta Clip, and Klemisan, 14-section, unmarked, can be marked with THERMOMARK CARD and BLUEMARK, color: white



### Key Commercial Data

|                                      |          |
|--------------------------------------|----------|
| Packing unit                         | 1 pc     |
| Minimum order quantity               | 10 pc    |
| Weight per Piece (excluding packing) | 2.0 g    |
| Custom tariff number                 | 39269097 |
| Country of origin                    | Poland   |

### Technical data

#### Dimensions

|            |       |
|------------|-------|
| Length (b) | 10 mm |
| Width (a)  | 8 mm  |

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 120 °C |
|---------------------------------|-------------------|

#### General

|  |  |
|--|--|
| Color                                  | white                                    |
| Components                             | free from silicone, halogen, and cadmium |
| Flammability rating according to UL 94 | V2                                       |
| Material                               | PC                                       |
| Wipe resistance                        | DIN EN 61010-1 (VDE 0411-1)              |
| Number of individual labels            | 14                                       |
| Number of individual labels per row    | 7  |
| Number of marker strips                | 2  |
| RoHS compliant                         | Yes                                      |
| Printability                           | Thermal transfer                         |
| Device                                 | 5146464 THERMOMARK CARD                  |

## Marker for terminal blocks - UM1-TM (8X10) - 0830906

### Technical data

#### General

|   |                                  |
|---|----------------------------------|
| Ink ribbon  | 0801371 THERMOMARK-RIBBON 110-TC |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02             |
| Result  | Test passed                      |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03     |
| Test duration   | 96 h                             |
| Wipe resistance test result   | Test passed                      |
| Salt spray test specification                                       | DIN EN 60068-2-11:2000-02        |
| Test duration   | 96 h                             |
| Salt spray testing result   | Test passed                      |
| Alternating condensation climate with SO2 test specification        | DIN 50018:2013-05                |
| Climate level   | AHT 1.0 S                        |
| Cycles  | 2                                |
| Condensation test result  | Test passed                      |
| Wipe resistance of test specification inscriptions                  | IEC 61010-1:2010-06              |
| Result  | Test passed                      |
| Marking mounting type   | clip on                          |

#### Standards and Regulations

|  |                             |
|--|-----------------------------|
| Wipe resistance                        | DIN EN 61010-1 (VDE 0411-1) |
| Flammability rating according to UL 94 | V2                          |

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |
| eCl@ss 9.0 | 27141137 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |