

## Cable marker carrier - LM - 1004377

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


Cable marker carrier, white, unlabeled, Mounting type: Assembly with cable binders, Cable diameter: 1-12 mm, Lettering field: 24 x 4 mm



### Product Features

- An insert label is placed inside the sealing cap to protect the labeling against dirt
- Plastic cable markers for marking and bundling conductors and cables indoors

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	100 pc
GTIN	 4 017918 012069
Weight per Piece (excluding packing)	0.91 g
Custom tariff number	39269097
Country of origin	Germany

### Technical data

#### Dimensions

Width (a)	24 mm
Cable diameter	1 mm ... 12 mm

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

#### General

Color	white
Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Material	PA
Marking mounting type	Assembly with cable binders

## Cable marker carrier - LM - 1004377

### Classifications

#### eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27400401
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

#### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001530

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410