


Replacement die - CF 500/DIE TC 4 - 1212237

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Die for crimping machine CF 500, for turned contacts with pin diameters of 2.5 and 4.0 mm (CK 2.5 ... CK 4.0) 0.14 ... 4 mm²

Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 449816
GTIN	4046356449816
Weight per Piece (excluding packing)	60.000 g
Custom tariff number	84799070
Country of origin	Germany

Technical data

Dimensions

Cable diameter	0.5 mm ... 2.4 mm
----------------	-------------------

General

Color	black
Compression	Square crimp
Material	Steel
Min. cross section	0.14 mm ²
Max. cross section	4 mm ²

Replacement die - CF 500/DIE TC 4 - 1212237

Classifications

eCl@ss

eCl@ss 10.0.1	17139201
eCl@ss 11.0	17130192
eCl@ss 4.0	21043000
eCl@ss 4.1	21043000
eCl@ss 5.0	21059000
eCl@ss 5.1	21059000
eCl@ss 6.0	21049000
eCl@ss 7.0	21049090
eCl@ss 9.0	17139201

ETIM

ETIM 3.0	EC001186
ETIM 4.0	EC001282
ETIM 6.0	EC001282
ETIM 7.0	EC001282

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	27111518
UNSPSC 13.2	27111518
UNSPSC 18.0	27111518
UNSPSC 19.0	27111518
UNSPSC 20.0	27111518
UNSPSC 21.0	27111518

Approvals

Approvals

Approvals

EAC

Ex Approvals

Replacement die - CF 500/DIE TC 4 - 1212237

Approvals

Approval details

EAC		RU C- DE.AI30.B.01549
-----	---	--------------------------

Accessories

Accessories

Cover

Covering hood - CF 500/COV RCI - 1212255



Protective cover for crimping machine CF 500, for insulated cable lugs 0.14 - 6 mm² (RCI 1.5/6) and turned contacts 0.14 - 4 mm² (TC 4)