

## Marker pin Zack strip - BN-ZB 7,5/WH:UNBEDRUCKT - 1401844


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Marker pin Zack strip, Strip, white, unlabeled, can be labeled with: Plotter, Mounting type: Plug in, for terminal block width: 7.5 mm, Lettering field: 6 x 4 mm

The illustration shows version BN-ZB 7,5 -UNPRINTED, - CONSEC. NOS and BNB-ZB 7,5 SO/CMS

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 020583
Weight per Piece (excluding packing)	0.52 g
Custom tariff number	39269097
Country of origin	Germany

### Technical data

#### Dimensions

Width (a)	6 mm
-----------	------

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

#### General

Note	Can be labeled with CMS
Color	white
Components	free from silicone and halogen
Flammability rating according to UL 94	V2
Material	PA
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	10
Number of individual labels per row	10

## Marker pin Zack strip - BN-ZB 7,5/WH:UNBEDRUCKT - 1401844

### Technical data

#### General

Number of marker strips	10
Marking mounting type	Plug in

### Classifications

#### eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

#### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410