

## Housing - HC-EVO-B10-CHWS-PLRBK - 1407640

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON EVO coupling housing, plastic, with bayonet flange for EVO screw connection, B10, with single locking latch, height: 90 mm, without EVO screw connection

### Why buy this product

- Flexible cable outlet direction, lateral or straight
- Lower costs than metal version
- Labeling option using 9 x 20 mm marking label
- Low weight
- Lower risk of condensation
- Both contact insert PE sheets are connected by means of a metal frame integrated in the sleeve housing
- Metal inlays ensure leading PE contact with angled plugs
- Completely corrosion-resistant
- Halogen-free plastic
- Marking label can be attached

### Key Commercial Data

Packing unit	1 STK
GTIN	 4 046356 777025
GTIN	4046356777025
Weight per Piece (excluding packing)	120.000 g
Custom tariff number	85389099
Country of origin	Poland

### Technical data

#### Dimensions

## Housing - HC-EVO-B10-CHWS-PLRBK - 1407640

### Technical data

#### Dimensions

Height	90 mm
Width	44 mm
Length	73 mm

#### Ambient conditions

Degree of protection of housing (IP)	IP66
Degree of protection of housing (NEMA)	12 (UL 50)
Ambient temperature (operation)	-40 °C ... 125 °C

#### General

Note	For contact inserts HC-B10, BB18, DD42, M, K8/24, HV03-I-PT, HC- 3-E...C
Size	B10
Housing type	Coupling housings
Color	black
Locking type	With single locking latch
No. of cable outlets	1
Cable exit	straight
	lateral
Screw connection	none
Housing material	Polyamide
Seal material	NBR
Material lock	Polyamide
Flammability rating according to UL 94	V0
Connection	The coupling housing must be supplemented with the EVO screw connection. The EVO screw connection is available in four sizes. The EVO screw connection is mounted with the aid of a pipe wrench, for example.


#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

### Drawings

# Housing - HC-EVO-B10-CHWS-PLRBK - 1407640

Dimensional drawing



Dimensional drawing

## Approvals

Approvals

---

Approvals

GL / EAC

---

Ex Approvals

---

## Approval details

GL <http://www.gl-group.com/newbuilding/approvals/index.html> 6196614

EAC 7500651.22.01.00246

---