

## Housing - HC-STA-B16-CHWS-1TTM32-ELC-AL - 1412646

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Coupling housings B16, With single locking latch, Material: Die-cast aluminum, salt water resistant, Cable outlets: 1, straight, Height: 79 mm, Cable gland: none, Gland: no, 1x M32, Standard

### Why buy this product

- good shielding in the event of electromagnetic interference



### Key Commercial Data

|                                      |   |
|--------------------------------------|---|
| Packing unit                         | 1 STK   |
| GTIN                                 | <br>4 055626 058917 |
| GTIN                                 | 4055626058917   |
| Weight per Piece (excluding packing) | 260.000 g   |
| Custom tariff number                 | 85389099  |
| Country of origin                    | China   |

### Technical data

#### Dimensions

|        |         |
|--------|---------|
| Height | 79 mm   |
| Width  | 44 mm   |
| Length | 93.5 mm |

#### Ambient conditions

|  |            |
|--|------------|
| Degree of protection of housing (IP)   | IP66       |
|  | IP67       |
| Degree of protection of housing (NEMA) | 4 (UL 50e) |

# Housing - HC-STA-B16-CHWS-1TTM32-ELC-AL - 1412646

## Technical data

### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
|                                 | 4X (UL 50e)       |
|                                 | 12 (UL 50e)       |
| Ambient temperature (operation) | -40 °C ... 125 °C |

### General

|                              |   |
|------------------------------|---|
| Note                         | For contact inserts HC-B16, BB32, D40, DD72, HS6, HV6, M, K |
| Size                         | B16   |
| Housing type                 | Coupling housings   |
| Color                        | silver  |
| Locking type                 | With single locking latch                                   |
| No. of cable outlets         | 1   |
| Cable exit                   | straight  |
| Screw connection             | none  |
| Type of the screw connection | 1x M32  |
| Housing material             | Die-cast aluminum, salt water resistant                     |
| Housing surface material     | Uncoated  |
| Seal material                | NBR, conductive   |
| Material lock                | PA  |

## Approvals

### Approvals

#### Approvals

EAC / GL / UL Recognized / cUL Recognized / cULus Recognized





#### Ex Approvals

### Approval details

|     |  |                     |
|-----|--|---------------------|
| EAC |  | 7500651.22.01.00246 |
|-----|--|---------------------|

# Housing - HC-STA-B16-CHWS-1TTM32-ELC-AL - 1412646

## Approvals

|                  |   |   |            |
|------------------|---|---|------------|
| GL               |  | <a href="http://exchange.dnv.com/tari/">http://exchange.dnv.com/tari/</a>   | 6196614 HH |
| UL Recognized    |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | E255026    |
| cUL Recognized   |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> | E255026    |
| cULus Recognized |  | <a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a> |            |