

Adapter - HC-B-TA-NPT-3/4-PLR-BK - 1414252

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Adapter, plastic, for EVO housing, NPT 3/4" thread



Key Commercial Data

Packing unit	1 STK
GTIN	 4 055626 022154
GTIN	4055626022154
Weight per Piece (excluding packing)	40.000 g
Custom tariff number	85389099
Country of origin	Poland

Technical data

Dimensions

Length of internal thread	15 mm
---------------------------	-------

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

General

Material	PA
Housing material	PA
Thread type on connection side	Bayonet B plastic
Thread type on seal side	3/4 inch NPT
Torque	10 Nm (Tightening torque of screw connection to be screwed in)
Flammability rating according to UL 94	V0

Adapter - HC-B-TA-NPT-3/4-PLR-BK - 1414252

Technical data

General

Assembly instructions	Bayonet locking max. 3x can be removed
-----------------------	--

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		7500651.22.01.00246
-----	---	---------------------
