

Contact insert module - HC-M-06P-CT-M - 1414368

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Contact insert module, Number of positions: 6, Pin, Crimp connection, 830 V, 16 A, 0.5 mm² ... 4 mm², Application: Power

RoHS

Key Commercial Data

Packing unit	1 STK
Minimum order quantity	5 STK
GTIN	 4 055626 025216
GTIN	4055626025216
Weight per Piece (excluding packing)	12.000 g
Custom tariff number	85389099
Country of origin	Poland

Technical data

Dimensions

Height	39.2 mm
Width	34.2 mm
Length	14.6 mm

Electrical characteristics

Note	For HEAVYCON housing type B6 to B48, HC-M-B...MF... hinged module carrier frame required, CK2,5-ED... imp contacts, crimp contacts not supplied as standard.
Rated voltage (III/3)	830 V
Rated current	16 A
Rated surge voltage	8 kV

Contact insert module - HC-M-06P-CT-M - 1414368

Technical data

Electrical characteristics

Connection profile	6
--------------------	---

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Mechanical characteristics

Conductor cross section	0.5 mm ² ... 4 mm ²
Connection cross section AWG	20 ... 12
Stripping length of the individual wire	7.5 mm
Insertion/withdrawal cycles	≥ 500
Minimum housing height	52 mm

General

Series	HC-M-06
Color	light gray
Number of module slots	1
Connection method	Crimp connection
Flammability rating according to UL 94	V0
Degree of pollution	3
Overvoltage category	III
Assembly instructions	Housing height ≥ 52 mm. Plug-in connections may only be operated only when there is no load/voltage.

Material data

Contact material	Copper alloy
Contact surface material	Ag (alternatively Au)
Contact carrier material	PC


Standards and Regulations

Flammability rating according to UL 94	V0
--	----


Drawings

Contact insert module - HC-M-06P-CT-M - 1414368

Schematic diagram




Dimensional drawing



Connector pin assignment, connection side

Diagram



Derating diagram (6 modules in HC-B 24 housing)

Classifications

eCl@ss

eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 8.0	27440205
eCl@ss 9.0	27440217

ETIM

ETIM 5.0	EC000438
ETIM 6.0	EC000438

UNSPSC

UNSPSC 13.2	39121421
-------------	----------

Approvals

Approvals

Contact insert module - HC-M-06P-CT-M - 1414368

Approvals

Approvals

EAC / UL Recognized / CSA

Ex Approvals

Approval details

EAC			7500651.22.01.00246
-----	--	--	---------------------

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E118976
mm ² /AWG/kcmil		12	
Nominal current I _N		24 A	
Nominal voltage U _N		830 V	

CSA		http://www.csagroup.org/services/testing-and-certification/certified-product-listing/	13631
mm ² /AWG/kcmil		12	
Nominal current I _N		18 A	
Nominal voltage U _N		830 V	

Accessories

Accessories

Assembly tool

Contact removal tool - CK2,5-EWZ - 1662722



Contact removal tool, for turned CK 2,5... contacts

Contact insert module - HC-M-06P-CT-M - 1414368

Accessories

Crimp contact

Crimp contact - CK2,5-ED-0,50ST AG - 1663572



Turned 2.5 crimp contact, individual male contact, core diameter 0.5 mm², silver-plated

Crimp contact - CK2,5-ED-0,75ST AG - 1663585



Turned 2.5 crimp contact, individual male contact, core diameter 0.75 mm², silver-plated

Crimp contact - CK2,5-ED-1,00ST AG - 1663598



Turned 2.5 crimp contact, individual male contact, core diameter 0.75 to 1.00 mm², silver-plated

Crimp contact - CK2,5-ED-1,50ST AG - 1663608



Turned 2.5 crimp contact, individual male contact, core diameter 1.5 mm², silver-plated

Crimp contact - CK2,5-ED-2,50ST AG - 1663611



Turned 2.5 crimp contact, individual male contact, core diameter 2.5 mm², silver-plated

Contact insert module - HC-M-06P-CT-M - 1414368

Accessories

Crimp contact - CK2,5-ED-3,00ST AG - 1663624



Turned 2.5 crimp contact, individual male contact, core diameter 3.00 mm², silver-plated

Crimp contact - CK2,5-ED-4,00ST AG - 1663637



Turned 2.5 crimp contact, individual male contact, core diameter 4.00 mm², silver-plated

Crimp contact - CK2,5-ED-0,50ST AU - 1674804



Turned 2.5 crimp contact, individual male contact, core diameter 0.5 mm², gold-plated

Crimp contact - CK2,5-ED-1,00ST AU - 1674781



Turned 2.5 crimp contact, individual male contact, core diameter 0.75 to 1.0 mm², gold-plated

Crimp contact - CK2,5-ED-1,50ST AU - 1674778



Turned 2.5 crimp contact, individual male contact, core diameter 1.5 mm², gold-plated

Contact insert module - HC-M-06P-CT-M - 1414368

Accessories

Crimp contact - CK2,5-ED-2,50ST AU - 1674817



Turned 2.5 crimp contact, individual male contact, core diameter 2.5 mm², gold-plated

Crimp contact - CK2,5-ED-4,00ST AU - 1674794



Turned 2.5 crimp contact, individual male contact, core diameter 4.00 mm², gold-plated

Crimping tool

Crimping pliers - CRIMPFOX-1,6/2,5-ED-4,0 - 1687419



Crimping pliers, for turned contacts, CK 1.6 ED... and CK 2.5 ED...

Module carrier frame

Module carrier frame - HC-M-B06-MF-B - 1417398



Module carrier frame, Size: B6, Type: for the panel mounting side (a, b, c, ...), 4 mm² ... 6 mm², Application: Module carrier frame

Module carrier frame - HC-M-B10-MF-B - 1417399



Module carrier frame, Size: B10, Type: for the panel mounting side (a, b, c, ...), 4 mm² ... 6 mm², Application: Module carrier frame

Contact insert module - HC-M-06P-CT-M - 1414368

Accessories

Module carrier frame - HC-M-B16-MF-B - 1417400



Module carrier frame, Size: B16, Type: for the panel mounting side (a, b, c, ...), 4 mm² ... 6 mm², Application: Module carrier frame

Module carrier frame - HC-M-B24-MF-B - 1417402



Module carrier frame, Size: B24, Type: for the panel mounting side (a, b, c, ...), 4 mm² ... 6 mm², Application: Module carrier frame

Module carrier frame - HC-M-B06-MF-H - 1417403



Module carrier frame, Size: B6, Type: for the sleeve side (A, B, C, ...), 4 mm² ... 6 mm², Application: Module carrier frame

Module carrier frame - HC-M-B10-MF-H - 1417404



Module carrier frame, Size: B10, Type: for the sleeve side (A, B, C, ...), 4 mm² ... 6 mm², Application: Module carrier frame

Module carrier frame - HC-M-B16-MF-H - 1417405



Module carrier frame, Size: B16, Type: for the sleeve side (A, B, C, ...), 4 mm² ... 6 mm², Application: Module carrier frame

Contact insert module - HC-M-06P-CT-M - 1414368

Accessories

Module carrier frame - HC-M-B24-MF-H - 1417406



Module carrier frame, Size: B24, Type: for the sleeve side (A, B, C, ...), 4 mm² ... 6 mm², Application: Module carrier frame

CK2,5-ED-0,37ST AG - 1585650



Phoenix Contact 2017 © - all rights reserved
<http://www.phoenixcontact.com>