

## Protective covers - HC-B16-BCSFD-P-BK - 1414629

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Protective cover B16, for double locking latch, protective cover material: PA, height: 18.5 mm, seal: no, diameter of retaining cord eyelet: 40 mm



COMPLETE

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 055626 030807
GTIN	4055626030807
Weight per Piece (excluding packing)	32.000 g
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### Dimensions

Length	97 mm
Width	46 mm
Height	18.5 mm
Diameter of retaining cord eyelet	40 mm

#### Ambient conditions

Degree of protection (IP)	IP66
Ambient temperature (operation)	-20 °C ... 100 °C

#### General

Size	B16
------	-----

# Protective covers - HC-B16-BCSFD-P-BK - 1414629

## Technical data

### General

Material	PA
Flammability rating according to UL 94	HB
Color	black
Seal present	no
Note	Protective cover for supporting base element with double locking latch
Connection	Plastic protective cover for short-term protection

### Standards and Regulations


Flammability rating according to UL 94	HB
--	----

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Drawings

Dimensional drawing



Dimensional drawing

## Classifications

eCl@ss

eCl@ss 10.0.1	27440208
eCl@ss 4.0	23110100

# Protective covers - HC-B16-BCSFD-P-BK - 1414629

## Classifications

### eCl@ss

eCl@ss 4.1	23110100
eCl@ss 5.0	23110100
eCl@ss 5.1	23110100
eCl@ss 6.0	27261200
eCl@ss 7.0	27440208
eCl@ss 8.0	27440208
eCl@ss 9.0	27440208

### ETIM

ETIM 5.0	EC002314
ETIM 6.0	EC002314
ETIM 7.0	EC002314

### UNSPSC

UNSPSC 13.2	39121421
UNSPSC 18.0	39121421
UNSPSC 19.0	39121421
UNSPSC 20.0	39121421
UNSPSC 21.0	39121421

## Approvals

### Approvals

---

#### Approvals

EAC

---

#### Ex Approvals

---

### Approval details

EAC		RU C- DE.AI30.B.01102
-----	---	--------------------------