

## Cable gland - HC-B-GM8X6,5-M40-ET-AL - 1414650

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




EVO metal cable gland with bayonet locking; size M40, for 8 conductors with 6.5 mm cable diameter



COMPLETE

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 031026
GTIN	4055626031026
Weight per Piece (excluding packing)	140.000 g
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### Dimensions

External cable diameter	6.5 mm ... 6.6 mm (Cable 1 ... 8)
-------------------------	-----------------------------------

#### Ambient conditions

Degree of protection (IP)	IP66 (Cable diameter 6.5 mm +0.1 mm)
Degree of protection (NEMA)	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Ambient temperature (operation)	-30 °C ... 100 °C

#### General

Type of the screw connection	M40
No. of conductors	8

# Cable gland - HC-B-GM8X6,5-M40-ET-AL - 1414650

## Technical data

### General

Material	Die-cast aluminum, corrosion-resistant
Housing material	Die-cast aluminum, corrosion resistant
Cable gland material	Aluminum
Material, pressure screw	Brass
Shielded	no
Color	silver

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

## Drawings

Dimensional drawing



Dimensional drawing

# Cable gland - HC-B-GM8X6,5-M40-ET-AL - 1414650

## Classifications

### eCl@ss

eCl@ss 10.0.1	27144432
eCl@ss 4.0	27140800
eCl@ss 4.1	27140800
eCl@ss 5.0	27149100
eCl@ss 5.1	27143400
eCl@ss 6.0	27149100
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109
eCl@ss 9.0	27144432

### ETIM

ETIM 5.0	EC000441
ETIM 6.0	EC000441
ETIM 7.0	EC000441

### UNSPSC

UNSPSC 13.2	39121311
UNSPSC 18.0	39121311
UNSPSC 19.0	39121311
UNSPSC 20.0	39121311
UNSPSC 21.0	39121311

## Approvals

### Approvals

---

#### Approvals


EAC-RoHS / EAC

---

#### Ex Approvals

---

### Approval details

EAC-RoHS		RU D- DE.HB35.B.00387
----------	-------------------------------------------------------------------------------------	--------------------------

## Cable gland - HC-B-GM8X6,5-M40-ET-AL - 1414650

### Approvals

EAC



RU C-  
DE.AI30.B.01102

### Accessories

#### Accessories

#### Sealing plugs

Closing cap - SEALING PLUG 7X16 RD - 1400255



Closing cap, material: PA, color: red