

## Cable gland - HC-B-GB-M40-ER-AL - 1414666


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Set consisting of: EVO metal adapter 1414259 and metal screw connection with bending armor rod 1415185, M40



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 055626 031170
GTIN	4055626031170
Weight per Piece (excluding packing)	680.000 g
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### Dimensions

Wrench size, union nut	46 mm
Wrench size, support	46 mm
External cable diameter	16 mm ... 28 mm

#### Ambient conditions

Degree of protection (IP)	IP66
	IP67
Ambient temperature (operation)	-40 °C ... 100 °C

#### General

Type of the screw connection	M40
Type	with bend protection sleeve

# Cable gland - HC-B-GB-M40-ER-AL - 1414666

## Technical data

### General

No. of conductors	1
Cable gland material	Nickel-plated brass
Material, pressure screw	Nickel-plated brass
Sealing material	EPDM (Screw connection)
Shielded	no
Thread type on connection side	Bayonet B metal
Color	silver

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

## Classifications

### eCl@ss

eCl@ss 5.1	27143400
eCl@ss 6.0	27149100
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109
eCl@ss 9.0	27144432

### ETIM

ETIM 5.0	EC000441
ETIM 6.0	EC000441
ETIM 7.0	EC000441

### UNSPSC

UNSPSC 13.2	39121311
-------------	----------

## Approvals

### Approvals

Approvals

EAC

## Cable gland - HC-B-GB-M40-ER-AL - 1414666

### Approvals

Ex Approvals

---

#### Approval details

EAC



RU C-  
DE.AI30.B.01102