

## Membrane screw connection - MG-INC-M16-S67L-PTES-LG - 1415186


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Membrane screw connection, cable gland material: Polypropylene, application: Standard, external cable diameter 4 mm ... 10 mm, shielding: no, connecting thread: M16, color: light gray



### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	20 pc
GTIN	 4 055626 038001
GTIN	4055626038001
Weight per Piece (excluding packing)	4.000 g
Custom tariff number	39269097
Country of origin	Germany

### Technical data

#### Dimensions

Length	15 mm
Length without connecting thread	7 mm
Connecting thread diameter	16 mm
Hexagon angular dimension	32 mm
Length of the connecting thread	8 mm
Feed-through hole diameter	16 mm ... 16.7 mm
External cable diameter	4 mm ... 10 mm

#### Ambient conditions

Degree of protection (IP)	IP66
	IP67

# Membrane screw connection - MG-INC-M16-S67L-PTES-LG - 1415186

## Technical data

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 65 °C
---------------------------------	------------------

### General

Cable gland material	Polypropylene
Seal material	TPE
Shielded	no
Thread type connection side	M16
Thread type on connection side	M16
Color	light gray
Assembly instructions	for 0.8 mm ... 3.5 mm wall thickness, for 16 mm ... 16.7 mm bore hole
Manufacturer	WISKA
Manufacturer Designation	CLIXX 16

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 5.1	27149100
eCl@ss 6.0	27379200
eCl@ss 7.0	27379216
eCl@ss 8.0	27379216
eCl@ss 9.0	27144433

### ETIM

ETIM 5.0	EC002024
ETIM 6.0	EC002024
ETIM 7.0	EC002024

### UNSPSC

UNSPSC 13.2	32151802
-------------	----------