

Extension adapter - A-INE-PG13/16-N-NS-S - 1415219


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Extension adapter, Cable gland material: Nickel-plated brass, Nickel-plated brass, Connecting thread: Pg13.5, Color: silver

The figure shows version A-INE-PG16/21-N-NS-S

Key Commercial Data

Packing unit	1
GTIN	 4 055626 038629
GTIN	4055626038629
Custom tariff number	74153900

Technical data

Dimensions

Length	19 mm
Length without connecting thread	12.5 mm
Connecting thread diameter	21 mm
Hexagon angular dimension	24 mm
Length of the connecting thread	6.5 mm

Ambient conditions

Degree of protection	IP65 (Depends on the screw connection used)
Ambient temperature (operation)	-20 °C ... 80 °C

General

Material	Nickel-plated brass
Cable gland material	Nickel-plated brass

Extension adapter - A-INE-PG13/16-N-NS-S - 1415219

Technical data

General

O-ring material	NBR
Outer thread	Pg13.5
Internal thread	Pg16
Color	silver

Drawings

Dimensional drawing

