

Contact insert module - HC-M-02-EMC-M - 1417374

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Contact insert module, Number of positions: 2, Pin, 50 V, 10 A, Application: Data/signal, for using two HC-M-EMV-ST/3-9,5 EMC connectors (pin version, each 4-pos.)



Key Commercial Data

Packing unit	1 STK
Minimum order quantity	2 STK
GTIN	 4 055626 112565
GTIN	4055626112565
Weight per Piece (excluding packing)	10.000 g
Custom tariff number	85389099
Country of origin	Poland

Technical data

Dimensions

Height	34 mm
Width	34.2 mm
Length	29.4 mm

Electrical characteristics

Note	For HEAVYCON housing type B6 to B48, HC-M-B...MF... hinged module carrier frame required.
Rated voltage (III/3)	50 V
Rated current	10 A
Rated surge voltage	0.8 kV
Connection profile	2

Contact insert module - HC-M-02-EMC-M - 1417374

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Mechanical characteristics

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

General

Series	HC-M-EMV
Color	light gray
Number of module slots	2
Flammability rating according to UL 94	V0
Degree of pollution	3
Overvoltage category	III
Assembly instructions	Housing height ≥ 72 mm. Plug-in connections may only be operated only when there is no load/voltage.
Connection	Plastic module for the HC-M-EMV-ST/3-9.5 EMC connector

Material data


Contact carrier material	PC
--------------------------	----

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Drawings

Dimensional drawing



Male insert

Classifications

eCl@ss

eCl@ss 5.1	27143424
eCl@ss 6.0	27143424

Contact insert module - HC-M-02-EMC-M - 1417374

Classifications

eCl@ss

eCl@ss 8.0	27440205
eCl@ss 9.0	27440218

ETIM

ETIM 5.0	EC000438
ETIM 6.0	EC000438

UNSPSC

UNSPSC 13.2	39121421
-------------	----------

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		7500651.22.01.00246
-----	--	---------------------

Accessories

Accessories

Module carrier frame

Module carrier frame - HC-M-B06-MF-B - 1417398



Module carrier frame, Size: B6, Type: for the panel mounting side (a, b, c, ...), 4 mm² ... 6 mm², Application: Module carrier frame

Contact insert module - HC-M-02-EMC-M - 1417374

Accessories

Module carrier frame - HC-M-B10-MF-B - 1417399



Module carrier frame, Size: B10, Type: for the panel mounting side (a, b, c, ...), 4 mm² ... 6 mm², Application: Module carrier frame

Module carrier frame - HC-M-B16-MF-B - 1417400



Module carrier frame, Size: B16, Type: for the panel mounting side (a, b, c, ...), 4 mm² ... 6 mm², Application: Module carrier frame

Module carrier frame - HC-M-B24-MF-B - 1417402



Module carrier frame, Size: B24, Type: for the panel mounting side (a, b, c, ...), 4 mm² ... 6 mm², Application: Module carrier frame

Module carrier frame - HC-M-B06-MF-H - 1417403



Module carrier frame, Size: B6, Type: for the sleeve side (A, B, C, ...), 4 mm² ... 6 mm², Application: Module carrier frame

Module carrier frame - HC-M-B10-MF-H - 1417404



Module carrier frame, Size: B10, Type: for the sleeve side (A, B, C, ...), 4 mm² ... 6 mm², Application: Module carrier frame

Contact insert module - HC-M-02-EMC-M - 1417374

Accessories

Module carrier frame - HC-M-B16-MF-H - 1417405



Module carrier frame, Size: B16, Type: for the sleeve side (A, B, C, ...), 4 mm² ... 6 mm², Application: Module carrier frame

Module carrier frame - HC-M-B24-MF-H - 1417406



Module carrier frame, Size: B24, Type: for the sleeve side (A, B, C, ...), 4 mm² ... 6 mm², Application: Module carrier frame