

Cable gland - G-INVEN-M20-M67N-PNES-BK - 1424537

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland, Cable gland material: PA, External cable diameter 6 mm ... 12 mm, Shielding: No, Connecting thread: M20


Product Description

Cable gland with pressure compensation element and flat gasket

Why buy this product

- reduces the formation of condensation
-

Key Commercial Data

Packing unit	1
GTIN	 4 055626 374420
GTIN	4055626374420
Custom tariff number	39269097

Technical data

Dimensions

Length	40 mm
Wrench size, union nut	24 mm
Wrench size, support	24 mm
Length of the connecting thread	10 mm
Feed-through hole diameter	25.1 mm ... 25.2 mm
External cable diameter	6 mm ... 12 mm
	6 mm ... 12 mm (for UL 514 B)

Cable gland - G-INVEN-M20-M67N-PNES-BK - 1424537

Technical data

Ambient conditions

Degree of protection	IP67
	IP66
Ambient temperature (operation)	-20 °C ... 100 °C (static)

General


Cable gland material	PA
Cable seal material	CR
Shielded	No
Thread type on connection side	M20
Thread pitch	1.5 mm
Torque	4 Nm (Union nut)
	4 Nm (Support)
	5 Nm (for UL514 B: union nut / support)
Flammability rating according to UL 94	V2
Impact category	5
Execution of the strain relief	A
Manufacturer	BIMED
Manufacturer Designation	BMVG-22

Standards and Regulations

Flammability rating according to UL 94	V2
--	----

Drawings

Dimensional drawing



Dimensional drawing

Classifications

eCl@ss

eCl@ss 5.1	27149109
------------	----------

Cable gland - G-INVEN-M20-M67N-PNES-BK - 1424537

Classifications

eCl@ss

eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109
eCl@ss 9.0	27144432

ETIM

ETIM 5.0	EC000441
----------	----------

Approvals

Approvals

Approvals

UL Recognized / cUL Recognized / EAC / cULus Recognized

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E199260
---------------	--	---	---------

cUL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E199260
----------------	--	---	---------

EAC			EAC-Zulassung
-----	--	--	---------------

cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	
------------------	--	---	--

Accessories

Accessories

Cable gland - G-INVEN-M20-M67N-PNES-BK - 1424537

Accessories

Flat nut

Nut - A-INL-M20-P-BK - 1411215



Nut, PA, for threads M20, Color: jet black RAL 9005

Sealing plugs

Closing cap - SEALING PLUG 9X16 RD - 1400259



Closing cap, for closing unused bore holes in multiple seals and cable glands, diameter 9 mm