


## Sensor/actuator cable - SAC-4P-100,0-180/0,34 - 1501786

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable ring, PUR halogen-free orange, 4-pos., conductor colors: Brown / white / blue / black, cable length: 100 m

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 813499
GTIN	4017918813499

### Technical data

#### Dimensions

Length of cable	100 m
-----------------	-------

#### General

Number of positions	4
---------------------	---

#### Cable

Cable type	PUR halogen-free orange
Cable type (abbreviation)	180
Cable abbreviation	Li31Y-11Y
Conductor cross section	0.34 mm <sup>2</sup>
AWG signal line	22
Conductor structure signal line	42x 0.10 mm
Core diameter including insulation	1.55 mm ±0.05 mm
Thickness, insulation	0.39 mm (Core insulation)
	0.75 mm (Outer cable sheath)
Wire colors	brown, white, blue, black
Overall twist	4 wires, twisted
External sheath, color	orange RAL 2003
External cable diameter	5.20 mm

## Sensor/actuator cable - SAC-4P-100,0-180/0,34 - 1501786

### Technical data

#### Cable

Smallest bending radius, fixed installation	52 mm
Smallest bending radius, movable installation	78 mm
Number of bending cycles	4000000
Bending radius	78 mm
Traversing path	10 m
Traversing rate	3 m/s
Acceleration	10 m/s <sup>2</sup>
Cable weight	35 kg/km
Outer sheath, material	PUR
Material conductor insulation	TPE
Conductor material	Bare Cu litz wires
Conductor resistance	≤ 57.5 Ω/km
Test voltage, cable	2500 V
Ambient temperature (operation)	-25 °C ... 105 °C (cable, fixed installation)
	-5 °C ... 105 °C (cable, flexible installation)

---

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>