

Contact insert - HC-A10-I-PT-F - 1585362

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Contact insert, Size: D15, Number of positions: 10+PE, Socket, Push-in connection, 250 V, 20 A, 0.14 mm² ... 2.5 mm²

RoHS

Key Commercial Data

Packing unit	1
GTIN	 4 046356 285094
GTIN	4046356285094
Custom tariff number	85369010

Technical data

General

Note	for housing HC-D15
Connection method	Push-in connection
Screwdriver blade	0.5 x 3.5 mm
Degree of pollution	3
Overvoltage category	III
Number of positions	10+PE
Insertion/withdrawal cycles	≥ 500
Size	D15
Conductor cross section	0.14 mm² ... 2.5 mm² (Applies to stranded conductors with ferrules)
Connection cross section AWG	26 ... 14
Stripping length of the individual wire	8 mm
Assembly instructions	Connectors may be operated only when there is no load/voltage.

Ambient conditions

Contact insert - HC-A10-I-PT-F - 1585362

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C (including heating up of contacts)
---------------------------------	--

Material data

Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC

Electrical characteristics


Rated voltage (III/3)	250 V
Rated surge voltage	4 kV
	4 kV
Rated current	20 A

Standards and Regulations

Flammability rating according to UL 94	V0
--	----


Drawings

Schematic diagram



Connector pin assignment, connection side


Dimensional drawing



Female insert

Contact insert - HC-A10-I-PT-F - 1585362

Dimensional drawing



Panel cutout

Approvals

Approvals

Approvals

GL / EAC / CSA / UL Recognized

Ex Approvals

Approval details

GL		http://exchange.dnv.com/tari/	6196614 HH
----	---	---	------------

EAC			EAC-Zulassung
-----	---	--	---------------

CSA		http://www.csagroup.org/services/testing-and-certification/certified-product-listing/	13631
mm²/AWG/kcmil		14	
Nominal current I _N		14 A	
Nominal voltage U _N		600 V	

Contact insert - HC-A10-I-PT-F - 1585362

Approvals

UL Recognized			http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E118976
mm²/AWG/kcmil		14		
Nominal current I _N		17 A		
Nominal voltage U _N		600 V		