

Crimp contact - SL-1CKP040 - 1607914

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimp contact, turned, contact diameter: 10 mm, crimp range: 35 mm² ... 35 mm²

The figure may differ depending on the connection area

Your advantages

- Crimping connection: vibration- and temperature-resistant assembly
- High tensile strength of the connection
- Low contact resistance
- Easy production monitoring



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	4 pc
GTIN	 4 046356 272858
GTIN	4046356272858
Weight per Piece (excluding packing)	1.000 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

General

Contact type	turned
Contact diameter	10 mm
Type of contact	Pin
Connection method	Crimp connection

Crimp contact - SL-1CKP040 - 1607914

Technical data

General


Insertion/withdrawal cycles mechanical	100
Litz wire cross section min.	35 mm ²
Litz wire cross section max.	35 mm ²
Contact material	Copper alloy
Contact surface	Silver

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Dimensional drawing



Classifications

eCl@ss

eCl@ss 10.0.1	27440204
eCl@ss 4.0	27260700
eCl@ss 4.1	27260700
eCl@ss 5.0	27260700
eCl@ss 5.1	27261200
eCl@ss 6.0	27261200
eCl@ss 7.0	27440204
eCl@ss 8.0	27440204
eCl@ss 9.0	27440204

Crimp contact - SL-1CKP040 - 1607914

Classifications

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC000796
ETIM 5.0	EC000796
ETIM 6.0	EC000796
ETIM 7.0	EC000796

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404
UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	39121522
UNSPSC 18.0	39121522
UNSPSC 19.0	39121522
UNSPSC 20.0	39121522
UNSPSC 21.0	39121522

Accessories

Accessories

Crimping tool

Crimping tool, electro-hydraulic - SL-Z0007 - 1613484

Crimping tool, electro-hydraulic



Crimping stamp - SL-Z0014 - 1613491

Crimping stamp for electro-hydraulic crimping device SL-Z0007 for turned crimp contacts, Ø 10 mm, SL series, crimping range 35 mm²



