

## Crimp contact - SB-36KS003 - 1623379

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimp contact, turned, Single contact, Contact diameter: 3.6 mm, Crimp range: 4 mm<sup>2</sup>...6 mm<sup>2</sup>

### Why buy this product

- Crimping connection: vibration- and temperature-resistant assembly
- High tensile strength of the connection
- Low contact resistance
- Easy production monitoring

### Key Commercial Data

|                      |   |
|----------------------|---|
| Packing unit         | 1   |
| GTIN                 | <br>4 055626 195230 |
| GTIN                 | 4055626195230   |
| Custom tariff number | 85366990  |

### Technical data

#### General

|  |                   |
|--|-------------------|
| Contact type                           | turned            |
| Contact diameter                       | 3.6 mm            |
| Type of contact                        | Socket            |
| Connection method                      | Crimp connection  |
| Insertion/withdrawal cycles mechanical | 100               |
| Litz wire cross section min.           | 4 mm <sup>2</sup> |
| Litz wire cross section max.           | 6 mm <sup>2</sup> |
| Contact material                       | CuZn              |

# Crimp contact - SB-36KS003 - 1623379

## Technical data

### General

|                 |  |
|-----------------|--|
| Contact surface | Nickel-plated (Ni), with gold coating (Au) |
|-----------------|--|

### Environmental Product Compliance

|            |   |
|------------|---|
| China RoHS | Environmentally Friendly Use Period = 50  |
|            | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |

## Drawings

Dimensional drawing

