

Crimp contact - RC-15S2000 - 1623775

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Crimp contact, turned, Contact diameter: 1.5 mm, Crimp range: 0.5 mm²...1 mm²

Why buy this product

- Crimping connection: vibration- and temperature-resistant assembly
- High tensile strength of the connection
- Low contact resistance
- Easy production monitoring



Key Commercial Data

| | |
|------------------------|----------|
| Packing unit | 1 STK |
| Minimum order quantity | 100 STK |
| Custom tariff number | 85369010 |
| Country of origin | Germany |

Technical data

General

| | |
|--|---------------------|
| Contact type | turned |
| Contact diameter | 1.5 mm |
| Type of contact | Socket |
| Connection method | Crimp |
| Insertion/withdrawal cycles mechanical | 100 |
| Litz wire cross section min. | 0.5 mm ² |
| Litz wire cross section max. | 1 mm ² |
| Contact material | CuZn |

Environmental Product Compliance

Crimp contact - RC-15S2000 - 1623775

Technical data

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally Friendly Use Period = 50 |
| | For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration" |