

## Crimp contact - RC-15P2010 - 1623776

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Crimp contact, turned, Contact diameter: 1 mm, Crimp range: 0.08 mm<sup>2</sup>...0.22 mm<sup>2</sup>

### Why buy this product

- Crimping connection: vibration- and temperature-resistant assembly
- High tensile strength of the connection
- Low contact resistance
- Easy production monitoring

### Key Commercial Data

Packing unit	1
GTIN	 4 055626 190259
GTIN	4055626190259
Custom tariff number	85369010

### Technical data

#### General

Contact type	turned
Contact diameter	1 mm
Type of contact	Pin
Connection method	Crimp connection
Insertion/withdrawal cycles mechanical	100
Litz wire cross section min.	0.08 mm <sup>2</sup>
Litz wire cross section max.	0.22 mm <sup>2</sup>

## Crimp contact - RC-15P2010 - 1623776

### Technical data

#### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"