

Cable gland - VC-M-KV-PG21/M32 ST - 1644397

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cable gland for Pg21 half screw connection to M32 housing entry, metal



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 904715
Weight per Piece (excluding packing)	60.13 g
Custom tariff number	85369010
Country of origin	Poland

Technical data

Dimensions

Wrench size, union nut	30 mm
External cable diameter	Depending on rubber seal

General

Material	Brass, nickel-plated
O-ring material	NBR
Thread type on connection side	M32
Thread type on seal side	Pg21
Torque	7.5 Nm

Cable gland - VC-M-KV-PG21/M32 ST - 1644397

Classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

EAC / EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Cable gland - VC-M-KV-PG21/M32 ST - 1644397

Approvals

EAC

Drawings

Dimensional drawing

