

Protective covers - HC-B 10-SD-FLU/FS-AL - 1644562

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON protective cover, type B10, for supporting base element with single locking latch, with retaining cord, IP65, ALU



Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	67.72 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Diameter of retaining cord eyelet	30 mm
-----------------------------------	-------

Ambient conditions

Degree of protection	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

General

Type	B10
	For supporting base element with single locking latch
Material	Aluminum, die-cast
Seal present	no
Connection	The guide pins of the protective cover must be removed when using coding sockets, pins, and bolts.

Protective covers - HC-B 10-SD-FLU/FS-AL - 1644562

Classifications

eCl@ss

eCl@ss 4.0	27141210
eCl@ss 4.1	27141210
eCl@ss 5.0	27149110
eCl@ss 5.1	27149110
eCl@ss 6.0	27261210
eCl@ss 7.0	27440208
eCl@ss 8.0	27440208
eCl@ss 9.0	27440208

ETIM

ETIM 2.0	EC000241
ETIM 3.0	EC002040
ETIM 4.0	EC002314
ETIM 5.0	EC002314

UNSPSC

UNSPSC 6.01	30212113
UNSPSC 7.0901	39121712
UNSPSC 11	39121712
UNSPSC 12.01	39121712
UNSPSC 13.2	39121712

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

Protective covers - HC-B 10-SD-FLU/FS-AL - 1644562

Approvals

EAC

Drawings

Dimensional drawing

