

Extension adapter - ENLAR-M-KV-M16/M20 - 1647653


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Step-up adapter, M16 to M20, including O-ring



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 947101
Weight per Piece (excluding packing)	14.5 g
Custom tariff number	74153300
Country of origin	Germany

Technical data

Dimensions

Length	17.5 mm
Length without connecting thread	11.5 mm
Connecting thread diameter	16 mm
Hexagon angular dimension GRP	22 mm
Length of the connecting thread	6 mm

Ambient conditions

Degree of protection	IP65 (Depends on the screw connection used)
Ambient temperature (operation)	-20 °C ... 80 °C

General

Material	Nickel-plated brass
Cable gland material	Nickel-plated brass

Extension adapter - ENLAR-M-KV-M16/M20 - 1647653

Technical data

General

O-ring material	NBR
Outer thread	M16
Internal thread	M20
Color	silver

Classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27439207

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000938

UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

Approvals

Approvals

Approvals

EAC

Ex Approvals

Extension adapter - ENLAR-M-KV-M16/M20 - 1647653

Approvals

Approvals submitted

Approval details

EAC

Drawings

Dimensional drawing

