

Adapter plate - VS-ADP24-VS09/VS09-GS-BU/BU - 1652499

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Adapter plate, size B24, reinforced, including panel mounting frame with DSUB 9 protective cover and gender changer contact insert socket/socket, and panel mounting frame with DSUB 9 protective cover and gender changer contact insert socket/socket



Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4017918960575

Technical data

Mechanical characteristics

Degree of protection	IP54
Type	B24

Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
---------------------------------	------------------

Material data

Flammability rating according to UL 94	HB
Material	PA
Sealing material	TPE
Seal material	TPE

Standards and Regulations

Flammability rating according to UL 94	HB
--	----


Environmental Product Compliance

China RoHS	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
------------	---

Drawings


Adapter plate - VS-ADP24-VS09/VS09-GS-BU/BU - 1652499

Dimensional drawing



Protective cover for D-SUB

Dimensional drawing



Mounting cutout

Phoenix Contact 2019 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>