

Cover plate - HC-B 16-AP-GY - 1660384


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON cover plate, for panel cutouts of type B16/HV6, 3.5 mm thick, gray



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 022020
GTIN	4017918022020
Weight per Piece (excluding packing)	18.100 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length	123 mm
Height	3.5 mm
Hole diameter	4.5 mm
Width	52 mm
Drill hole distance, horizontal	103 mm
Drill hole distance, vertical	32 mm

General

Note	For panel cutouts of type B16/HV6
Material	PA
Flammability rating according to UL 94	HB

Cover plate - HC-B 16-AP-GY - 1660384

Technical data

General

Color	gray
Type	B16
	HV6

Standards and Regulations

Flammability rating according to UL 94	HB
----------------------------------------	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 5.1	27143400
eCl@ss 6.0	27261200
eCl@ss 7.0	27440201
eCl@ss 8.0	27440201
eCl@ss 9.0	27440201

ETIM

ETIM 3.0	EC002309
ETIM 4.0	EC000886
ETIM 5.0	EC002309
ETIM 6.0	EC002309
ETIM 7.0	EC002309

UNSPSC

UNSPSC 6.01	30211817
UNSPSC 7.0901	39121416
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	31261501