

## Adapter plate - HC-B 24-ADP-B 6-GY - 1660407


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON adapter plate, type B24 on B6, for panel cutouts of type B24, gray

The figure shows a version of the product

### Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 022044
GTIN	4017918022044
Weight per Piece (excluding packing)	37.690 g
Custom tariff number	39269097
Country of origin	Germany

### Technical data

#### Dimensions

Length	150 mm
Height	7 mm
Hole diameter	4.5 mm
Width	52 mm
Drill hole distance, horizontal	130 mm
Drill hole distance, vertical	27 mm

#### General

Note	For panel cutouts of type B24, cannot be used for panel mounting bases having a pre-mounted protective cover
------	--

# Adapter plate - HC-B 24-ADP-B 6-GY - 1660407

## Technical data

### General

Material	PA
Flammability rating according to UL 94	HB
Color	gray
Type	B24
Assembly instructions	Cannot be used in panel mounting bases having a pre-mounted cover

### Standards and Regulations

Flammability rating according to UL 94	HB
--	----

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 5.1	27143400
eCl@ss 6.0	27261200
eCl@ss 7.0	27440201
eCl@ss 8.0	27440201
eCl@ss 9.0	27440201

### ETIM

ETIM 3.0	EC002309
ETIM 4.0	EC002309
ETIM 5.0	EC002309
ETIM 6.0	EC002309
ETIM 7.0	EC002309

### UNSPSC

UNSPSC 6.01	30211817
UNSPSC 7.0901	39121416
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	31261501

## Approvals

### Approvals

## Adapter plate - HC-B 24-ADP-B 6-GY - 1660407

### Approvals

Approvals

EAC

---

Ex Approvals

---

### Approval details

EAC		RU C- DE.AI30.B.01102
-----	---	--------------------------

---