

Adapter plate - HC-B 24-ADP-B 16-GY - 1660449


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON adapter plate, type B24 on B16, for panel cutouts of type B24, gray



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 022082
Weight per Piece (excluding packing)	32.31 g
Custom tariff number	39269097
Country of origin	Germany

Technical data

Dimensions

Length	150 mm
Hole diameter	4.5 mm
Width	52 mm
Drill hole distance, horizontal	130 mm
Drill hole distance, vertical	32 mm

General

Note	For panel cutouts of type B24, cannot be used for panel mounting bases having a pre-mounted protective cover
Material	PA
Flammability rating according to UL 94	HB
Color	light gray
Type	B24

Adapter plate - HC-B 24-ADP-B 16-GY - 1660449

Technical data

Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440201

ETIM

ETIM 3.0	EC002309
ETIM 4.0	EC002309
ETIM 5.0	EC002309

UNSPSC

UNSPSC 6.01	30211817
UNSPSC 7.0901	39121416
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Adapter plate - HC-B 24-ADP-B 16-GY - 1660449

Approvals

Approval details

EAC

Drawings

