

Adapter plate - HC-B 24-ADP-3RST-GY - 1662175


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Adapter plates with a reinforced wall, three openings for an M23 circular connector; type B24 on an M23 circular connector; for panel cutouts of type B24; gray



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	10 pc
GTIN	 4 017918 100087
GTIN	4017918100087
Weight per Piece (excluding packing)	37.900 g
Custom tariff number	85472000
Country of origin	Germany

Technical data

Dimensions

Length	150 mm
Height	7 mm
Hole diameter	4.5 mm
Width	52 mm
Drill hole distance, horizontal	130 mm
Drill hole distance, vertical	32 mm
Internal cutout dimension	3 x 21 mm

General

Note	For wall cutouts of type B24
Material	PA

Adapter plate - HC-B 24-ADP-3RST-GY - 1662175

Technical data

General

Flammability rating according to UL 94	HB
Color	gray
Type	B24

Standards and Regulations

Flammability rating according to UL 94	HB
--	----

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143400
eCl@ss 6.0	27261200
eCl@ss 7.0	27440201
eCl@ss 8.0	27440201
eCl@ss 9.0	27440201

ETIM

ETIM 3.0	EC002309
ETIM 4.0	EC002309
ETIM 5.0	EC002309
ETIM 6.0	EC002309
ETIM 7.0	EC002309

UNSPSC

UNSPSC 6.01	30211817
UNSPSC 7.0901	39121416
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	31261501

