

RJ45 bending protection sleeve - VS-08-KS/GR - 1689213

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



RJ45 bend protection sleeve, for pin insert VS-08-ST-RJ45, cable cross section up to 6 mm, color: gray



Key Commercial Data

Packing unit	1 pc
Minimum order quantity	5 pc
Weight per Piece (excluding packing)	6.33 g
Custom tariff number	39269097
Country of origin	United States

Technical data

Mechanical characteristics

External cable diameter	6 mm
Color	gray

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C
---------------------------------	------------------

Material data

Flammability rating according to UL 94	V0
Housing material	PA

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

RJ45 bending protection sleeve - VS-08-KS/GR - 1689213

Classifications

eCl@ss

eCl@ss 4.0	27141210
eCl@ss 4.1	27141210
eCl@ss 5.0	27149110
eCl@ss 5.1	27149110
eCl@ss 6.0	27149110
eCl@ss 7.0	27149110
eCl@ss 8.0	27440212

ETIM

ETIM 2.0	EC000241
ETIM 3.0	EC002040
ETIM 4.0	EC002040
ETIM 5.0	EC001680

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

RJ45 bending protection sleeve - VS-08-KS/GR - 1689213

Drawings

Dimensional
drawing

RJ45
bending
protection
sleeve

Phoenix Contact 2016 © - all rights reserved
<http://www.phoenixcontact.com>