

Protective covers - HC-B 6-TMS-SD-IP50 - 1690736


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Protective cover B6, Clip locking, protective cover material: PA, height: 31.2 mm, seal: no, With lanyard, Diameter of retaining cord eyelet: 4 mm

RoHS

Key Commercial Data

Packing unit	1 STK
Minimum order quantity	10 STK
GTIN	 4 017918 890629
GTIN	4017918890629
Weight per Piece (excluding packing)	33.090 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Length	90 mm
Width	55 mm
Height	31.2 mm
Diameter of retaining cord eyelet	3.5 mm

Ambient conditions

Degree of protection	IP50
Ambient temperature (operation)	-20 °C ... 100 °C

General

Size	B6
------	----

Protective covers - HC-B 6-TMS-SD-IP50 - 1690736

Technical data

General

Type	HC-ADVANCE protective cover
Flammability rating according to UL 94	V0
Color	gray
Seal present	no

Standards and Regulations


Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Dimensional drawing



Dimensional drawing

Classifications

eCl@ss

eCl@ss 4.0	27141210
eCl@ss 4.1	27141210
eCl@ss 5.0	27142104
eCl@ss 5.1	27142104
eCl@ss 6.0	27142104
eCl@ss 7.0	27142104
eCl@ss 8.0	27440208
eCl@ss 9.0	27440208

ETIM

ETIM 2.0	EC000241
ETIM 3.0	EC002040
ETIM 4.0	EC002040
ETIM 5.0	EC002314
ETIM 6.0	EC002314

Protective covers - HC-B 6-TMS-SD-IP50 - 1690736

Classifications

UNSPSC

UNSPSC 6.01	30212113
UNSPSC 7.0901	39121712
UNSPSC 11	39121712
UNSPSC 12.01	39121712
UNSPSC 13.2	39121421

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01102
-----	---	--------------------------
