

Printed-circuit board connector - PTF 0,3/ 4-BB-8-H - 1707559

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Direct connector - PTF, rated voltage (III/2): 25 V, number of positions: 4, pitch: 1.8 mm, color: white, contact surface: Tin, mounting: Direct plug-in method, For flexible PCBs with a width of 8 mm and a permissible PCB thickness in the contact zone of 0.15 mm ... 0.3 mm

Why buy this product

- ✓ Tool-free fast connection for flexible PCBs
- ✓ Small component size for applications where space is at a premium
- ✓ Reliable contacting of flexible PCBs, thanks to fixing pin
- ✓ Designed and tested according to IEC 60838-2-2



Key Commercial Data

Packing unit	1 STK
Minimum order quantity	25 STK
GTIN	 4 046356 934237
GTIN	4046356934237
Weight per Piece (excluding packing)	2.400 g
Custom tariff number	85366930
Country of origin	Poland

Technical data

Dimensions

Length [l]	8 mm
Width [w]	9.2 mm
Height [h]	4.8 mm
Pitch	1.8 mm

Printed-circuit board connector - PTF 0,3/ 4-BB-8-H - 1707559

Technical data

General

Range of articles	PTF 0,3/...-BB-H
Type of contact	Female connector
Number of positions	4
Insulating material group	IIIa
Rated voltage (III/3)	< 25 V
Rated voltage (III/2)	25 V
Nominal cross section	0.34 mm ²
Maximum load current	10 A (Total current of all contacts)
Insulating material	PBT
Flammability rating according to UL 94	V0

Standards and Regulations


Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance


China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Drilling diagram




Diagram



Type: PTF 0,3/ 4-BB-8-H

Dimensional drawing



Printed-circuit board connector - PTF 0,3/ 4-BB-8-H - 1707559

Classifications

eCl@ss

eCl@ss 5.1	27141190
eCl@ss 6.0	27141190
eCl@ss 8.0	27440309
eCl@ss 9.0	27440309

ETIM

ETIM 4.0	EC002643
ETIM 5.0	EC002637
ETIM 6.0	EC002638

UNSPSC

UNSPSC 13.2	39121432
-------------	----------

Approvals


Approvals


Approvals

UL Recognized / EAC

Ex Approvals

Approval details

UL Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E118976-20130430
mm ² /AWG/kcmil	22		
Nominal current I _N	5 A		
Nominal voltage U _N	60 V		

EAC		B.01742
-----	---	---------

Printed-circuit board connector - PTF 0,3/ 4-BB-8-H - 1707559

Accessories

Additional products

Printed-circuit board connector - PTF 0,3/ 4-WB-8-H - 1707561




Printed-circuit board connector, 4-position

Printed-circuit board connector - PTF 0,3/ 2-WB-8-H - 1707558



Printed-circuit board connector, 2-position

PCB - PTF 0,3/ 4-FLEX-I-8 - 1848477



Accessories, number of positions: 4, pitch: 1.8 mm, color: white, mounting: PCB connector

PCB - PTF 0,3/ 4-FLEX-L-8 - 1848480



Accessories, number of positions: 4, pitch: 1.8 mm, color: white, mounting: PCB connector

PCB - PTF 0,3/ 4-FLEX-T-8 - 1848493



Accessories, number of positions: 4, pitch: 1.8 mm, color: white, mounting: PCB connector
